

Water softener **EFFEGI BREGA** Technical info.

Dear customer,

the function of the softener is to make the water purer for the laboratory.

The resin softener (DVA / 8 - Easy) essentially breaks down calcium and magnesium ions.

So we have softened water. The biggest advantage is the absence of calcium that with time creates encrustations that wear and damage the equipment.

The water softener is a device with low purchase and management costs: to keep it active it is sufficient to make every 500 liters of water a wash of the resins with 1 kg of salt.

(Common coarse kitchen salt for food use).

The so regenerated resins return to 100% of their ability to kill calcium and magnesium ions. We recommend a complete replacement of the resins every 6-8 years.

The model EASY, compared to the DVA / 8 is equipped with a liter counter clock to know the consumption of water. Both are equipped with a series of fittings and pipes to facilitate connection with the steamer. It is recommended for all steam generators where the water hardness exceeds the 10 ° f. Releases water with a calcium content lower than the 5 ° French optimal value for minimal fouling.




DVA/8



EASY



Resin replacement kit



Hardness test