# **STEAM BOX**

- Optional accessory-

This washing cabin allows to reduce the spread of vapor particles during the cleaning operations with steam generators. The stainless steel compact structure can easily be placed next to the steam generator.

It is equipped with a tank underneath for collecting decantation water but it can also be connected directly to the laboratory decanter.

This device allows to operate easily, while maintaining a clean working environment. It is provided with CE marking.

#### **WASHING CABIN**

#### Equipped with:

- · Double grid with filter
- Disposable non-woven fabric
- Support for muffles

## **CONTROL PANEL**

- ON/OFF switch
- Fan speed variator
- Power cable plug
- LED lighting of the working area



## **CHARACTERISTICS**

- Large washing chamber with rubber protection against accidental impact
- Low consumption LED lamp
- 24V DC fan



## **DISCHARGE TUBE**

- Provided with stopcock
- Can be oriented to the left or to the right
- Can be directly linked to the waste water drain