


- POLIMERIZATION UNIT -

POLYVALENT DIGITAL

The apparel with electronic control. A product that respects the tradition of solid, practical and long lasting. Used to hydroscopic bath, pressure hydroscopic, wax removal from cylinder, autoclave and press the coating of plaster.

Tanks

- Equipped with basket and stand with tweezers.
- Equipped with safety release to prevent the opening of the machine under pressure.



Utilisations

- Cures any type of resin.
- Bathroom hygroscopic.
- Bathroom hygroscopic pressure.
- Remove wax from the cvlinders.
- pressure cooker.
- Press plaster coating.
- Cooking in the oven, slow-cure resin.
- 10 programmable cycles.
- Timed Power.
- Programmable timer.
- In the event of temporary absence of voltage the unit will continue the cycle from where it left off.

Display



✓ Simple.

Display:

Start time cycle, pressure, temperature, maintenance, cooling, exhaust water-air.

Control buttons

- the planning of the various cycles.
- · Display of data set.
- Printing of the report cycle.
- The machine control.